

OCUTECH® SIGHTSCOPE® 2

The high-quality, easy to fit, easy to use bioptic telescope system

Available in two powers:

1.7x: Indicated for Visual Acuity of 20/50 or better
Field of view: 26° monocular; 32.5° binocular
Focus range: 5 feet (1.5m) to infinity
Catalog # A7717

2.2x: Indicated for Visual Acuity of 20/100 or better
Field of view: 18° monocular; 22.5° binocular
Focus range: 6 feet (1.8m) to infinity
Catalog # A7722

Easy 3-Step Fitting Method

1. Slide the telescope(s) right and left to align them for each eye
2. Adjust the nose pads to align the bottom of the telescope with the top of the pupil
3. Align the telescope viewing angle with the line of sight of the user

That's it!



Viewing angle adjustment method using Allen wrench supplied.



SightScope 2 Features:

- Exceptionally wide fields of view
- Crisp, bright optics
- Completely adjustable for PD and viewing angle
 - Re-adjustable even after dispensing
 - Re-usable
- Binocular or monocular options
- Built-in sunshield reduces glare and reflections
- No eyepiece corrections required!
- Flips out of the way when not needed!
- Simple to demonstrate, fit and prescribe
 - Use our Easy 3-step fitting method
- Frame mounted and clip-on options
 - Choose one of Ocutech's 3 frame styles
 - Selection of styles, sizes, colors
 - Patient clip system works on many frames
- Prescribe in bioptic or full-diameter positions
 - Bioptic position: Use Ocutech K or U frames
 - Full-diameter: Use Ocutech Sleek frame
- Carrier lens suggestions:
 - Prescribe plano lenses or normal distance Rx or bifocal if normally worn
- Reading caps for near working distances
 - Available powers:
 - +1, +1.5, +2, +2.5, +3, +4
 - Includes prism for binocular viewing
 - Custom powers by special order
- Slip-behind sunfilters in 4 standard colors
 - Gray, Brown, Blue-blocker, Yellow
- Step-by-step easy order forms
 - PDFs and online ordering

OCUTECH® Vision Enhancing Systems

OCUTECH, Inc. • 800 326-6460 • 919 967-6460 • www.ocutech.com • info@ocutech.com